


BALL-LOCK PILOT PIN, WITH TAPERED TIP, LIGHT DUTY

2262.




2262. Ball-Lock pilot pin, with tapered tip, light duty

d ₂ / Order No	d ₅	P	l ₁ / Order No	N	I (Order Code character)	71 (D)	80 (E)	90 (F)	100 (G)	110 (H)	125 (J)	140 (K)	150 (L)
10 / (2)	8	5,9 - 9,9	19(2)	8		●	●	●	●	●			
13 / (3)	8	9,9 - 12,9	19(2)	10		●	●	●	●	●	●		
16 / (4)	8	12,9 - 15,9	25(3)	15		●	●	●	●	●	●	●	●
20 / (5)	8	15,9 - 19,9	25(3)	20		●	●	●	●	●	●	●	●
25 / (6)	8	19,9 - 24,9	25(3)	25		●	●	●	●	●	●	●	●
32 / (7)	8	24,9 - 31,9	25(3)	30			●	●	●	●	●	●	●
38 / (8)	8	31,9 - 37,9	30(4)	35			●	●	●	●	●	●	●

Ordering Code (example):

2262.4G3.1410



Shape: round

P = Ø 14,1 mm

Punch cutting length: l₁
25 mm

Length: I
100 mm

Diameter: d₂
16 mm

Type:
light

Execution:
Pilot pin with tapered tip

Punch:
without ejector pin

= 1410

Order No
= (3)

Order Code character
= (G)

Order No
= (4)

Order No
= (2)

Order No
= (6)

= 22

Material:

HSS

Hardness 62 ± 2 HRC

Execution:

Shaft and pilot pin fine ground.

Special dimensions on request.