


SÜRTÜNME PLAKASI, ÇELİK YAĞ KANALLI, CNOMO



2960.44.45.



Malzeme:

Çelik, yüzeysel sertleştirilmiş

Not:


Civatalar dahil değildir.

Sabitleme:

Soket başlı vida kullanınız

DIN EN ISO 4762 M10.

2960.44.45.



SÜRTÜNME PLAKASI, ÇELİK YAĞ KANALLI, CNOMO

2960.44.45. Sürtünme Plakası, Çelik yağ kanallı, CNOMO

Sipariş No.	Şekil	b	a	e	e ₁	e ₂	e ₃	e ₄	e ₅	e ₆	e ₇	e ₈	e ₉	Vida Deliği adedi
2960.44.45.070.100	A	70	100	20	-	-	-	70	-	-	-	-	10	2
2960.44.45.070.150	B	70	150	10	20	-	-	70	120	-	-	-	10	3
2960.44.45.070.200	D	70	200	20	-	-	-	70	120	170	-	-	10	4
2960.44.45.100.100	I	100	100	30	50	-	-	45	70	-	-	-	25	3
2960.44.45.100.150	C	100	150	50	-	-	-	45	95	120	-	-	25	4
2960.44.45.100.200	D	100	200	50	-	-	-	70	120	170	-	-	25	4
2960.44.45.100.250	E	100	250	50	-	-	-	70	120	170	220	-	25	5
2960.44.45.100.300	F	100	300	50	-	-	-	70	120	170	220	270	25	6
2960.44.45.150.100	G	150	100	25	75	100	-	70	-	-	-	-	50	4
2960.44.45.150.150	H	150	150	25	75	100	-	45	95	120	-	-	50	4
2960.44.45.150.200	D	150	200	100	-	-	-	70	120	170	-	-	50	4
2960.44.45.150.250	E	150	250	100	-	-	-	70	120	170	220	-	50	5
2960.44.45.150.300	F	150	300	100	-	-	-	70	120	170	220	270	50	6
2960.44.45.200.100	G	200	100	50	100	150	-	70	-	-	-	-	75	4