



Special properties

- Material: Carbon fibre
- Roundness tolerance: $\pm 0,05$ mm
- Tolerance of diameter: $- 0,1$ mm
- Temperature: Max. 100 °C
- Colour: Black

- Mounting accessories on request

DryLin® Shafts

mm

Phone +49 - 22 03 - 96 49-145
 Fax +49 - 22 03 - 96 49-334



Dimensions [mm]

| Part No. | Version | Diameter [mm] -0,1 | Max. length [mm] | Weight [kg/m] |
|----------|--------------|-----------------------|------------------|---------------|
| CWM-12* | hollow shaft | 12/9 | 2000 mm | 0,07 |
| CWM-16* | hollow shaft | 16/12,5 | 2000 mm | 0,12 |
| CWM-20* | hollow shaft | 20/16 | 2000 mm | 0,17 |
| CWM-30* | hollow shaft | 30/26 | 2000 mm | 0,27 |

Order example: CWM-12, 500 corresponds to a carbon fibre shaft \varnothing 12 mm, 500 mm in length.

* Delivery time upon request