



KMA pivoting
KMA locking

Recommended for unsupported and gliding applications

Recommended for vertical hanging and standing applications

Width index	Part No. full set KMA pivoting	Part No. full set KMA locking	<i>Bi</i> [mm]	Width index	Part No. full set KMA pivoting	Part No. full set KMA locking	<i>Bi</i> [mm]
050. ▶	E4.380.050.12.C	E4.381.050.12.C	050	225. ▶	E4.380.225.12.C	E4.381.225.12.C	225
062. ▶	E4.380.062.12.C	E4.381.062.12.C	062	237. ▶	E4.380.237.12.C	E4.381.237.12.C	237
075. ▶	E4.380.075.12.C	E4.381.075.12.C	075	250. ▶	E4.380.250.12.C	E4.381.250.12.C	250
087. ▶	E4.380.087.12.C	E4.381.087.12.C	087	262. ▶	E4.380.262.12.C*	E4.381.262.12.C*	262
100. ▶	E4.380.100.12.C	E4.381.100.12.C	100	275. ▶	E4.380.275.12.C*	E4.381.275.12.C*	275
105. ▶	E4.380.105.12.C	E4.381.105.12.C	105	287. ▶	E4.380.287.12.C*	E4.381.287.12.C*	287
112. ▶	E4.380.112.12.C	E4.381.112.12.C	112	300. ▶	E4.380.300.12.C*	E4.381.300.12.C*	300
125. ▶	E4.380.125.12.C	E4.381.125.12.C	125	312. ▶	E4.380.312.12.C*	E4.381.312.12.C*	312
137. ▶	E4.380.137.12.C	E4.381.137.12.C	137	325. ▶	E4.380.325.12.C*	E4.381.325.12.C*	325
150. ▶	E4.380.150.12.C	E4.381.150.12.C	150	337. ▶	E4.380.337.12.C*	E4.381.337.12.C*	337
162. ▶	E4.380.162.12.C	E4.381.162.12.C	162	350. ▶	E4.380.350.12.C*	E4.381.350.12.C*	350
175. ▶	E4.380.175.12.C	E4.381.175.12.C	175	362. ▶	E4.380.362.12.C*	E4.381.362.12.C*	362
187. ▶	E4.380.187.12.C*	E4.381.187.12.C*	187	375. ▶	E4.380.375.12.C*	E4.381.375.12.C*	375
200. ▶	E4.380.200.12.C	E4.381.200.12.C	200	387. ▶	E4.380.387.12.C*	E4.381.387.12.C*	387
212. ▶	E4.380.212.12.C*	E4.381.212.12.C*	212	400. ▶	E4.380.400.12.C*	E4.381.400.12.C*	400

(KMA = polymer metal mounting bracket) For the C-profile option please add index **C**

*Width available upon request. Please consult igus® for delivery time.