

Option 2: Tiewrap plates with clip-on connection for the C-profile

Characteristic features: ● Can be plugged into the KMA C-profile ● Easy solvable with screwdriver ● Easy to assemble without any screws. Easy solvable with screwdriver nevertheless safe stop ● **Use:** single part for the manufacturing of switchgear cabinets or for the assembly of machines ● Accessory for igus® E-ChainSystems® ● For all E-Chains® with KMA and integrated C-profile

Part No.	Width [mm]	Number of teeth
3050.ZC	50	5
3075.ZC	75	7

For Series:

Tiewrap plates for C-profile

For all mounting brackets with C-Profil-option!



Strain relief

Option 3: Clip-on tiewrap plates for opening or fixed crossbars

Characteristic features: ● Can be plugged on the fixed crossbars ● In case of many harnessed cables with strain relief "over two floors" ● If the KMA is too small for the C-profile ● Easy to assemble without any screws ● **Use:** single part for the manufacturing of switchgear cabinets or for the assembly of machines ● Accessory for igus® E-ChainSystems®

Part No.	Width [mm]	Number of teeth	For Series
2050.Z	60	6	E/Z200, 2400/2500, 2600/2700
3050.Z	50	5	3400/3500
3075.Z	74	7	3400/3500

Part No.	Width [mm]	Number of teeth	For Series
2050.Z	60	6	E4/H4/R4.28, 220, 2650
3035.ZS	35	3	3400/3450/3500
3050.ZS	50	5	3400/3450/3500
3075.ZS	75	7	3400/3450/3500
3850.ZS	48	5	E4/H4/R4.32, E4/H4/R4.42, 14240/14340, 15250/15350, E6.52, E6.62
4550.ZS	48	5	E4/H4/R4.56, E4/H4/R4.80, 14040/14140/18840, 14550/14650/19050, 15050/15150/19850, E6.80L, E6.80
4575.ZS	74	7	E4/H4/R4.56, E4/H4/R4.80, 14040/14140/18840, 14550/14650/19050, 15050/15150/19850, E6.80L, E6.80

For Series:

For more details see table!



Phone +49- (0) 22 03-96 49-800
Fax +49- (0) 22 03-96 49-222



Option 4: integrated strain relief for E2 Tubes - Series R

Characteristic features: ● Strain relief disappears completely in the E-Tube ● Easy to assemble without any screws ● **Use:** single part for the manufacturing of switchgear cabinets or for the assembly of machines ● Accessory for igus® E-ChainSystems®

Part No.	Width of strain relief [mm]	Number of teeth	Series
3050.Z	50	5	R68
3075.Z	75	7	R68
5850.Z	46	4	R58

For Series:

E2 E-Tubes

● R58 ● R68

