

















Tragarmsystem CP 120

	drehbar/neigbar	starr	Länge mm	Gewicht kg	Farbe RAL	Gehäuseteil CP 120	Gehäuseteil CP 120/60	Mittelteil CP 120	Wandteil CP 120	
						Best.-Nr.				
Adapter CP 120/60 von Tragarmanschluss Ø 130 mm auf □ 120 x 65 mm										
	siehe Seite 157	-	■	-	0,5	7035	6212.500	6212.500	-	-
Befestigung CP 120/60 für Tragarmanschluss										
	Ø 130 mm	-	■	-	0,7	7035	6212.320	6206.320	-	-
	□ 120 x 65 mm	-	■	-	0,7	7035	-	6206.360	-	-
Kupplung CP 120/60 für Tragarmanschluss										
	Ø 130 mm	■	-	-	2,0	7035	6212.300	6206.300	-	-
	□ 120 x 65 mm	-	-	-	-	-	-	6206.340	-	-
Winkelkupplung 90° CP 120 für Tragarmanschluss										
	Ø 130 mm	■	-	-	2,1	7035/ 7024	6212.380	-	-	-
Tragprofil CP 120/60										
	geschlossen	-	-	250	2,0	7035	CP 120 6212.025	CP 60 ¹⁾ 6206.025	CP 120 6212.025	CP 120 6212.025
		-	-	500	3,9		6212.050	6206.050	6212.050	6212.050
		-	-	1000	7,8		6212.100	6206.100	6212.100	6212.100
		-	-	2000	15,6		6212.200	6206.200	6212.200	6212.200
	offen	-	-	500	4,6	7035/ 7024	6212.150	-	6212.150	6212.150
		-	-	1000	9,2		6212.110	-	6212.110	6212.110
		-	-	2000	18,4		6212.210	-	6212.210	6212.210
Adapter für Tragarm-Kombination CP 120/60										
	siehe Seite 159	-	■	-	0,7	7035	-	6212.640	-	-
Winkelstück 90° CP 120										
		-	■	-	1,1	7035/ 7024	6212.600	-	-	6212.600
Zwischengelenk CP 120										
		■	-	-	4,4	7035/ 7024	-	-	6212.620	-
Aufsatzgelenk CP 120										
	Abgang vertikal	■	-	-	3,8	7035	-	-	-	6212.720
	Abgang horizontal	■	-	-	4,3	7035/ 7024	-	-	-	6212.700
Wandgelenk CP 120										
	Abgang vertikal	■	-	-	5,5	7035/ 7024	-	-	-	6212.760
	Abgang horizontal	■	-	-	6,1	7035/ 7024	-	-	-	6212.740
Wand-/Bodenbefestigung CP 120, klein										
		-	■	-	0,5	7035	-	-	-	6212.820
Wand-/Bodenbefestigung CP 120, groß										
		-	■	-	2,5	7035/ 7024	-	-	-	6212.800
Montage-Element CP 120/180 für Signalsäule										
	siehe Seite 720	-	■	-	0,1	7024	6212.900	6212.900	6212.900	6212.900
Neigungsadapter										
Für Tragarmanschluss Ø 130 mm und □ 120 x 65 mm									siehe Seite 147	
Zubehör										
Adapter CP 120 auf Tragarm, höhenverstellbar 6071.600									siehe Seite 159	

¹⁾ Gewichtsangaben und Grafiken für CP 60, siehe Seite 147