

Interior installation

System lights

Universal light

With integral motion detector

Benefits:

- Insulated plastic housing
- Efficient compact fluorescent tube
- Simple attachment of the light to the enclosure

Material:

- Plastic

Supply includes:

- Mounting clips



Also required:

- Connection accessories, see page 639



Technical specifications	Socket	Width mm	Height mm	Depth mm	Model No.	Approvals
18 W, 110 – 240 V, 50 – 60 Hz	Earthing-pin	343	95	55	4155.110	VDE
	-	343	95	55	4155.010	VDE
	-	343	95	55	4155.510	UL

Courtesy light

Without door operated switch

Technical specifications	Socket	Width mm	Height mm	Depth mm	Model No.	Approvals
14 W, 100 – 240 V, 50/60 Hz	Earthing-pin	452	117	50	4139.140	ENEC
18 W, 100 – 240 V, 50/60 Hz	Earthing-pin	682	117	50	4139.180	ENEC
30 W, 100 – 240 V, 50/60 Hz	Earthing-pin	987	117	50	4139.300	ENEC

With door operated switch

Technical specifications	Socket	Width mm	Height mm	Depth mm	Model No.	Approvals
14 W, 100 – 240 V, 50/60 Hz	Earthing-pin	452	117	50	4139.150	ENEC
18 W, 100 – 240 V, 50/60 Hz	Earthing-pin	682	117	50	4139.190	ENEC
30 W, 100 – 240 V, 50/60 Hz	Earthing-pin	987	117	50	4139.350	ENEC



Also required:

- Connection accessories, see page 639



Standard light

Without door operated switch

Technical specifications	Socket	Width mm	Height mm	Depth mm	Model No.	Approvals
14 kW, 230 V, 50 Hz	Earthing-pin	452	117	50	4138.140	ENEC
18 W, 230 V, 50 Hz	Earthing-pin	682	117	50	4138.180	ENEC
30 W, 230 V, 50 Hz	Earthing-pin	987	117	50	4138.300	ENEC
14 W, 120 V, 60 Hz	USA	452	117	50	4138.240	cURus
18 W, 120 V, 60 Hz	USA	682	117	50	4138.280	cURus
30 W, 120 V, 60 Hz	USA	987	117	50	4138.400	cURus

With door operated switch

Technical specifications	Socket	Width mm	Height mm	Depth mm	Model No.	Approvals
14 W, 230 V, 50 Hz	Earthing-pin	452	117	50	4138.150	ENEC
18 W, 230 V, 50 Hz	Earthing-pin	682	117	50	4138.190	ENEC
30 W, 230 V, 50 Hz	Earthing-pin	987	117	50	4138.350	ENEC
14 W, 120 V, 60 Hz	USA	452	117	50	4138.250	cURus
18 W, 120 V, 60 Hz	USA	682	117	50	4138.290	cURus
30 W, 120 V, 60 Hz	USA	987	117	50	4138.450	cURus



Also required:

- Connection accessories, see page 639

