

Baying systems TS 8



System accessories Page 613 ISV assembly modules Page 381 TS enclosure (WxD 600 x 400/600 mm) Page 74

Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed
- Roof: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Door: Sheet steel, 2 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Rear panel: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Gland plates: Sheet steel, 1.5 mm, zinc-plated

Colour:

- RAL 7035

Basis of test:

- IEC 61 439-1/-2

Protection category IP to IEC 60 529:

- IP 55

Protection category NEMA:

- NEMA 12

Supply includes:

- Enclosure frame with door(s)
- Three-piece gland plates
- Rear panel
- Roof plate
- 4 eyebolts
- Lock: 3 mm double-bit

Distribution enclosures

Width mm	Packs of	850	850	1100	1100	Page
Height mm		2000	2000	2000	2000	
Depth mm		400	600	400	600	
Model No.	1 pc(s).	9666.955	9666.915	9666.965	9666.925	
Weight kg		111.0	117.0	146.0	156.0	
Door(s)		1	1	2	2	
Also required						
Installation kit	1 pc(s).	9666.911	9666.911	9666.921	9666.921	380
Mounting angle	2 pc(s).	9666.712	9666.712	9666.712	9666.712	387
Depth stay	2 pc(s).	-	-	9666.731	9666.731	387
Accessories						
Side panels, screw-fastened, sheet steel	2 pc(s).	8104.235	8106.235	8104.235	8106.235	643
Base/plinth components, front and rear, 100 mm	2 pc(s).	8601.850	8601.850	8601.300	8601.300	619
Base/plinth trim panels, side, 100 mm	2 pc(s).	8601.040	8601.060	8601.040	8601.060	620
Base/plinth components, front and rear, 200 mm	2 pc(s).	8602.850	8602.850	8602.100	8602.100	619
Base/plinth trim panels, side, 200 mm	2 pc(s).	8602.040	8602.060	8602.040	8602.060	620
Levelling feet	4 pc(s).	4612.000	4612.000	4612.000	4612.000	628
Roof plates for cable entry gland	1 pc(s).	9665.953	9665.913	9665.963	9665.923	693
Cable entry glands		see page	see page	see page	see page	694
Angular baying bracket	4 pc(s).	8800.430	8800.430	8800.430	8800.430	655
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	654