

## Installation accessories for modular front design

### Partial doors

The door may be optionally hinged on the right or left. The partial door is attached to the enclosure with no drilling required. In the case of partial doors without a viewing panel (height 600 – 1000 mm), the installation of a monitor frame 2305.000 is supported. Standard double-bit lock insert may be exchanged for lock inserts, type A.

#### Material:

- Partial door: Sheet steel, 2 mm
- Viewing window: 3 mm single-pane safety glass

#### Surface finish:

- Textured paint

#### Colour:

- RAL 7035

#### Supply includes:

- Cross member, hinges and lock components
- Assembly parts



#### Also required:

- Front trim panels, top, see page 116 or top-hinged trim panel, see page 117
- Front trim panels, bottom, see page 116



#### Accessories:

- Monitor frame 2305.000, see page 130
- Lock inserts, type A, see page 123
- Perforated mounting strips, see page 116

#### For enclosure width 400 mm

Height mm	With viewing window	P. of	Model No.
200	–	1 pc(s).	<b>9682.142</b>
300	–	1 pc(s).	<b>9682.143</b>
400	–	1 pc(s).	<b>9682.144</b>
600	–	1 pc(s).	<b>9682.146</b>
800	–	1 pc(s).	<b>9682.148</b>
1000	–	1 pc(s).	<b>9682.140</b>
1200	–	1 pc(s).	<b>9682.152</b>
1400	–	1 pc(s).	<b>9682.154</b>
1600	–	1 pc(s).	<b>9682.156</b>
1800	–	1 pc(s).	<b>9682.158</b>
2000	–	1 pc(s).	<b>9682.150</b>

#### For enclosure width 600 mm

Height mm	With viewing window	P. of	Model No.
150	–	1 pc(s).	<b>9682.161</b>
200	–	1 pc(s).	<b>9682.162</b>
300	–	1 pc(s).	<b>9682.163</b>
400	–	1 pc(s).	<b>9682.164</b>
600	–	1 pc(s).	<b>9682.166</b>
600	■	1 pc(s).	<b>9682.167</b>
800	–	1 pc(s).	<b>9682.168</b>
800	■	1 pc(s).	<b>9682.169</b>
1000	–	1 pc(s).	<b>9682.160</b>
1200	–	1 pc(s).	<b>9682.172</b>
1400	–	1 pc(s).	<b>9682.174</b>
1600	–	1 pc(s).	<b>9682.176</b>
1800	–	1 pc(s).	<b>9682.178</b>
2000	–	1 pc(s).	<b>9682.170</b>

#### For enclosure width 800 mm

Height mm	With viewing window	P. of	Model No.
150	–	1 pc(s).	<b>9682.181</b>
200	–	1 pc(s).	<b>9682.182</b>
300	–	1 pc(s).	<b>9682.183</b>
400	–	1 pc(s).	<b>9682.184</b>
600	–	1 pc(s).	<b>9682.186</b>
600	■	1 pc(s).	<b>9682.187</b>
800	–	1 pc(s).	<b>9682.188</b>
1000	–	1 pc(s).	<b>9682.180</b>
1200	–	1 pc(s).	<b>9682.192</b>
1400	–	1 pc(s).	<b>9682.194</b>
1600	–	1 pc(s).	<b>9682.196</b>
1800	–	1 pc(s).	<b>9682.198</b>
2000	–	1 pc(s).	<b>9682.190</b>

#### For enclosure width 1000 mm

Height mm	With viewing window	P. of	Model No.
400	–	1 pc(s).	<b>9682.104</b>
600	–	1 pc(s).	<b>9682.106</b>
800	–	1 pc(s).	<b>9682.108</b>

#### For enclosure width 1200 mm

Height mm	With viewing window	P. of	Model No.
400	–	1 pc(s).	<b>9682.124</b>
600	–	1 pc(s).	<b>9682.126</b>
800	–	1 pc(s).	<b>9682.128</b>

