

SERIES 34

PALIRED POLYAMIDE 6 OR POLYPROPYLENE FURNITURE WHEELS



Wheel description

Polyamide 6 or polypropilene.

Hub

The plain bearing bore results from a hole in the material forming the centre of the wheel and contains the axle.

Diameters: 35-100 mm

Carrying capacities: 10-40 daN

Fittings with swivel, fixed and swivel with brake brackets



Black polyamide 6 wheels, top plate and stem fittings

Top carrying capacity 30 daN

Diameters: 35 - 50 mm



White polyamide 6 wheels, top plate and stem fittings

Top carrying capacity 20 daN

Diameters: 50 mm



Transparent blue polyamide 6 wheels, top plate and stem fittings

Top carrying capacity 20 daN

Diameters: 50 mm



Gray polyamide 6 wheels, top plate and stem fittings

Top carrying capacity 40 daN

Diameters: 60 - 100 mm

Available also with brake

Uses

Environments

Suitable for indoor applications, without chemical aggressives. The series can be used for home and office furniture and chairs with light carrying capacity. Typical usage: office chairs and armchairs, hi-fi stands, flower boxes, metal furniture pieces.

Usage temperatures: from 0 °C to +40 °C

Floors



Handling

