

Gimbal expansion joint DN 90

Oper. pressure [bar]: 10

Oper. temp. range [K]: 20 ÷ 320

Oper. travel ranges (max.)
- angular [°] : ± 20

Weight (max) [Kg] : 10.6

Spring rates (max.)
- angular [N m/°] : 3

Operating fluids : LO2, LH2

Bellows material : AISI 316 L

Application : A5 EPC LBS lines

Status : Qualified for flight

