



KZ 1500




Compact Height



ORDER	S (mm)	L1 ±0.25 (mm)	L (mm)	Kg.
KZ 1500 013	13	78	65	1.17
KZ 1500 016	16	84	68	1.21
KZ 1500 019	19	90	71	1.25
KZ 1500 025	25	102	77	1.32
KZ 1500 032	32	116	84	1.41
KZ 1500 038	38	128	90	1.49
KZ 1500 050	50	152	102	1.64
KZ 1500 063	63	178	115	1.81
KZ 1500 075	75	202	127	1.97
KZ 1500 080	80	212	132	2.03
KZ 1500 100	100	252	152	2.29
KZ 1500 125	125	302	177	2.61



CODE	Pressure (bar/psi)	F ₀ (daN)	F ₁ (daN)
KZ 1500 050	150 / 2175	1530	2475
KZ-H 1500 050	0 / 0	---	---



N₂

S_{max} < 90%

V_{max} 1,6 m/s

P_{min} (20°C)
P_{max} (20°C)



























T_{min}
T_{max}

600 CP-


bar	psi	bar	psi	°C	°F	°C	°F	
20	290	150	2175	0	32	80	176	

KZ 1500 MOUNTS





Compact Height

								
								
								
MODEL	X CR 1500 CW 1500 KZ 1500	X	CT 1500 CK 1500	CM 1500 CD 1500	X	CPH 2800 CP 3000	CS 3000	
SERIES	MINI 	COMPACT HEIGHT 	THREADED 	LOW PROFILE 	HEAVY DUTY 	ISO 	HEAVY LOAD >Pmax 	POWER COMPACT STROKE <S >F0 

A14-063



A69-063




CODE	KZ 1500 050	KIT S-XXXXXXX KIT C-XXXXXXX	A14-063	18 CG 1-Q
ENG ORDER	GAS SPRING	REPAIR KIT	FLANGE	CHARGING ADAPTER
DEU BESTELLUNG	GASDRUCKFEDER	ERSATZTEILSATZ	FLANSCHEN	LADEADAPTER
FRA COMMANDE	RESSORT À GAZ	KIT DE RÉPARATION	BRIDE	RACCORD DE CHARGE
ITA ORDINE	CILINDRO AD AZOTO	KIT DI MANUTENZIONE	FLANGE	ADATTATORE DI CARICO
ESP PEDIDO	RESORTE DE GAS	KIT DE REPARACION	BRIDA	ADAPTADOR DE CARGA
POR PEDIDO	CILINDRO DE GÁS	KIT DE MANUTENÇÃO	FLANGE	ADAPTADOR DE CARGA

KZ 1500 MOUNTS


Compact Height




B36-063








B41-063



C05-063



C35-063




CODE	KZ 1500 050	KIT S-XXXXXXX KIT C-XXXXXXX	B36-063	18 CG 1-Q
ENG ORDER	GAS SPRING	REPAIR KIT	FLANGE	CHARGING ADAPTER
DEU BESTELLUNG	GASDRUCKFEDER	ERSATZTEILSATZ	FLANSCHEN	LADEADAPTER
FRA COMMANDE	RESSORT À GAZ	KIT DE RÉPARATION	BRIDE	RACCORD DE CHARGE
ITA ORDINE	CILINDRO AD AZOTO	KIT DI MANUTENZIONE	FLANGE	ADATTATORE DI CARICO
ESP PEDIDO	RESORTE DE GAS	KIT DE REPARACION	BRIDA	ADAPTADOR DE CARGA
POR PEDIDO	CILINDRO DE GAS	KIT DE MANUTENÇÃO	FLANGE	ADAPTADOR DE CARGA









KZ 1500 MOUNTS

Compact Height

D02-063



D67-063



CODE	KZ 1500 050	KIT S-XXXXXXX KIT C-XXXXXXX	D02-063	18 CG 1-Q
ENG ORDER	GAS SPRING	REPAIR KIT	FLANGE	CHARGING ADAPTER
DEU BESTELLUNG	GASDRUCKFEDER	ERSATZTEILSATZ	FLANSCHEN	LADEADAPTER
FRA COMMANDE	RESSORT À GAZ	KIT DE RÉPARATION	BRIDE	RACCORD DE CHARGE
ITA ORDINE	CILINDRO AD AZOTO	KIT DI MANUTENZIONE	FLANGE	ADATTATORE DI CARICO
ESP PEDIDO	RESORTE DE GAS	KIT DE REPARACION	BRIDA	ADAPTADOR DE CARGA
POR PEDIDO	CILINDRO DE GÁS	KIT DE MANUTENÇÃO	FLANGE	ADAPTADOR DE CARGA