




KZ 2400


Compact Height




ORDER	S (mm)	L1 ±0.25 (mm)	L (mm)	Kg.
KZ 2400 016	16	91	75	1.89
KZ 2400 019	19	97	78	1.94
KZ 2400 025	25	109	84	2.04
KZ 2400 032	32	123	91	2.16
KZ 2400 038	38	135	97	2.26
KZ 2400 050	50	159	109	2.47
KZ 2400 063 *	63	185	122	2.69
KZ 2400 075 *	75	209	134	2.90
KZ 2400 080 *	80	219	139	2.98
KZ 2400 100 *	100	259	159	3.33
KZ 2400 125 *	125	309	184	3.75



CODE		Pressure		F_0	F_1
		bar	psi	daN	daN
KZ 2400 050		150	2175	2385	3890
KZ-H 2400 050		0	0	---	---



	ENG ORDER DEU BESTELLUNG FRA COMMANDE ITA ORDINE ESP PEDIDO POR PEDIDO	F_0	S
		daN	mm
KZ 2400 50			
KZ 2400 50			



	$S_{max} < 90\%$	$V_{max} 1,6 \text{ m/s}$	 Pmin (20°C) Pmax (20°C)	 Tmin Tmax	
--	------------------	---------------------------	-----------------------------	---------------	--

N ₂	S _{max} < 90%	V _{max} 1,6 m/s	bar psi	bar psi	°C °F	°C °F	600 CP-
			20 290	150 2175	0 32	80 176	




KZ 2400 MOUNTS





Compact Height

	50	50	50	50	50	50	50	50
	Ø75	Ø75	Ø75	Ø75	Ø75	Ø75	Ø75	Ø75
	L1=137 L1=145 L1=159	L1=154 L1=160 L1=160	L1=185 L1=195 L1=210	L1=210	L1=175 L1=200	L1=240		
MODEL	×	CR 2400 CW 2400 KZ 2400	×	CT 2500 CK 2500 FD 1500	GN 1500 CM 2500 CD 2400	AG 1500	CPH 4300 CP 5000	CS 4700
SERIES	MINI	COMPACT HEIGHT	THREADED	LOW PROFILE	HEAVY DUTY	ISO	HEAVY LOAD	POWER COMPACT STROKE

A14-075



A34-075




CODE	KZ 2400 050	KIT S-XXXXXXX KIT C-XXXXXXX	A14-075	18 CG 1-Q
ENG ORDER	GAS SPRING	REPAIR KIT	FLANGE	CHARGING ADAPTER
DEU BESTELLUNG	GASDRUCKFEDER	ERSATZTEILSATZ	FLANSCHEN	LADEADAPTER
FRA COMMANDE	RESSORT À GAZ	KIT DE RÉPARATION	BRIDE	RACCORD DE CHARGE
ITA ORDINE	CILINDRO AD AZOTO	KIT DI MANUTENZIONE	FLANGE	ADATTATORE DI CARICO
ESP PEDIDO	RESORTE DE GAS	KIT DE REPARACION	BRIDA	ADAPTADOR DE CARGA
POR PEDIDO	CILINDRO DE GÁS	KIT DE MANUTENÇÃO	FLANGE	ADAPTADOR DE CARGA

KZ 2400 MOUNTS


Compact Height

AZOL
GAS


B13-075





B18-075



B23-075




B98-075



SEAL
KIT S-XXXXXXX

750
2150252
7/23CE art.3
XXXXXXXXXX
XXXXXXXXXX
Made in Spain (2175)
www.azolgas.com

CARTRIDGE
KIT C-XXXXXXX



CODE	KZ 2400 050	KIT S-XXXXXXX KIT C-XXXXXXX	B13-075	18 CG 1-Q
ENG ORDER	GAS SPRING	REPAIR KIT	FLANGE	CHARGING ADAPTER
DEU BESTELLUNG	GASDRUCKFEDER	ERSATZTEILSATZ	FLANSCHEN	LADEADAPTER
FRA COMMANDE	RESSORT À GAZ	KIT DE RÉPARATION	BRIDE	RACCORD DE CHARGE
ITA ORDINE	CILINDRO AD AZOTO	KIT DI MANUTENZIONE	FLANGE	ADATTATORE DI CARICO
ESP PEDIDO	RESORTE DE GAS	KIT DE REPARACION	BRIDA	ADAPTADOR DE CARGA
POR PEDIDO	CILINDRO DE GÁS	KIT DE MANUTENÇÃO	FLANGE	ADAPTADOR DE CARGA

