


圆柱销 于 DIN EN ISO 8734

2351.1.



材料:
 钢
 硬度 60 ± 2 HRC
 结构:
 渗碳硬化, 精磨。

2351.1. 圆柱销 于 DIN EN ISO 8734

d_1	l_2	r	l_1	4	5	6	8	10	12	14	16	18	20	22	24	26	28	30	32	36	40	45	50	55	60	70	80	90	100	120	
1	0.4	1		●	●	●	●	●	●																						
1.5	0.5	1.6		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
2	0.6	2		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
2.5	0.7	2.5		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
3	0.8	3		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
4	1	4			●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
5	1.2	5			●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
6	1.5	6				●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
8	1.8	8					●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
10	2	10						●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
12	2.5	12							●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
14	2.5	16								●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
16	3	16									●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
20	4	20										●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●

订购示例:

圆柱销 于 DIN EN ISO 8734 = 2351.1.
 直径 d_1 6 mm = 0600.
 长度 l_1 8 mm = 008
 订购编号 = 2351.1.0600.008