

# Cast aluminium enclosures GA



GA accessories Page 29 System accessories Page 507

**Material:**

- Enclosure: Cast aluminium
- Cover: Cast aluminium, all-round foamed-in PU seal

**Surface finish:**

- Textured paint

**Colour:**

- RAL 7001

**Protection category IP to IEC 60 529:**

- IP 66

**Protection category NEMA:**

- NEMA 4

**Supply includes:**

- Enclosure with cover
- Cover screws, captive
- Screws for attaching support rails
- Screw for connection of the PE conductor

**Technical details:**

Available on the Internet

Width mm		58	98	75	125	175	250	122	220	Page
Height mm		64	64	80	80	80	80	120	120	
Depth mm		34	35	57	57	57	57	80	91	
Model No.		<b>9101.210</b>	<b>9102.210</b>	<b>9104.210</b>	<b>9105.210</b>	<b>9106.210</b>	<b>9107.210</b>	<b>9108.210</b>	<b>9110.210</b>	
	Packs of	5 pc(s).	3 pc(s).	1 pc(s).	1 pc(s).	1 pc(s).	1 pc(s).	1 pc(s).	1 pc(s).	
<b>Accessories</b>										
Mounting plate		-	-	-	9105.700	-	-	9108.700	9110.700	29
	Packs of	-	-	-	10 pc(s).	-	-	2 pc(s).	2 pc(s).	
Wall mounting bracket	2 pc(s).	-	-	-	-	-	-	9121.122	9121.122	29
Hinge, exterior	2 pc(s).	-	-	-	-	-	-	9123.000	9123.000	29
Earth straps		see page	see page	see page	see page	see page	see page	see page	see page	644
Cable glands		from page	from page	from page	from page	from page	from page	from page	from page	658

Width mm	Packs of	360	160	260	360	202	280	334	330	Page
Height mm		120	160	160	160	232	232	233	230	
Depth mm		82	91	91	91	111	111	111	181	
Model No.	1 pc(s).	<b>9111.210</b>	<b>9112.210</b>	<b>9113.210</b>	<b>9114.210</b>	<b>9116.210</b>	<b>9117.210</b>	<b>9118.210</b>	<b>9119.210</b>	
<b>Accessories</b>										
Mounting plate		-	9112.700	9113.700	9114.700	9116.700	9117.700	9118.700	9118.700	29
	Packs of	-	2 pc(s).	2 pc(s).	1 pc(s).	1 pc(s).	1 pc(s).	1 pc(s).	1 pc(s).	
Wall mounting bracket	2 pc(s).	9121.122	9121.160	9121.160	9121.160	9121.230	9121.230	9121.230	9121.230	29
Hinge, exterior	2 pc(s).	9123.000	9123.000	9123.000	9123.000	9123.000	9123.000	9123.000	9123.000	29
Earth straps		see page	see page	see page	see page	see page	see page	see page	see page	644
Cable glands		from page	from page	from page	from page	from page	from page	from page	from page	658