

5113 Reducer long SDR11


Product information

Material

- PE100

Manufacture

- Injection moulded



Available items

ART.CODE	d	d1	L	L1	Z	e	e1	Verp
5113402510	25	20	45	45	103	2.3	2	50
5113403210	32	25	49	46	108.5	3	2.3	50
5113403220	32	20	49	46	106	3	2	50
5113404010	40	32	52	49	118	3.7	3	50
5113404020	40	25	54	45	113.5	3.7	2.3	50
5113404030	40	20	53	46	118	3.7	2	50
5113405010	50	40	57	54	131	4.6	3.7	20
5113405020	50	32	57	50	124	4.6	3	20
5113405030	50	25	57	47	127	4.6	2.3	20

Van de Lande BV

Lissenveld 1 \ 4941 VK Raamsdonksveer \ The Netherlands \ t +31 (0)162 51 60 00 \ f +31 (0)162 52 14 17 \ sales@vandelande.com
 Traderegister Tilburg: 18070844 \ IBAN: NL13 RABO 0143 0035 26 \ BIC: RABONL2U \ VAT: NL 8123.91.755.B01

ART.CODE	d	d1	L	L1	Z	e	e1	Verp
5113406310	63	50	67	60	152	5.8	4.6	5
5113406320	63	40	67	55	146	5.8	3.7	5
5113406330	63	32	67	51	149	5.8	3	5
5113407510	75	63	72	69	164	6.8	5.8	5
5113407520	75	50	72	59	155	6.8	4.6	5
5113409010	90	75	84	75	155	8.2	6.8	5
5113409020	90	63	84	68	178	8.2	5.8	5
5113411010	110	90	89	84	210	10	8.2	5
5113411020	110	75	89	75	196	10	6.8	5
5113411030	110	63	89	68	199	10	5.8	10
5113412510	125	110	94	89	207	11.4	10	13
5113412520	125	90	94	84	211	11.4	8.2	6
5113412540	125	63	92	68	214	11.4	5.8	6
5113414010	140	125	105	100	233	12.7	11.4	5
5113414020	140	110	105	90	240	12.7	10	5
5113416010	160	140	110	114	256	14.6	12.7	2
5113416020	160	125	110	100	238	14.6	11.4	2
5113416030	160	110	110	95	246	14.6	10	2
5113416040	160	90	110	89	259	14.6	8.2	2
5113418010	180	160	117	114	261	16.4	14.6	2
5113418030	180	125	117	97	263	16.4	11.4	2
5113418040	180	110	117	93	271	16.4	10	2
5113418050	180	90	117	89	283	16.4	8.2	2
5113420020	200	160	121	108	265	18.2	14.6	2
5113422520	225	180	130	115	287	20.5	16.4	1
5113422530	225	160	130	107	295	20.5	14.6	1

Van de Lande BV

Lissenveld 1 \ 4941 VK Raamsdonksveer \ The Netherlands \ t +31 (0)162 51 60 00 \ f +31 (0)162 52 14 17 \ sales@vandelande.com
 Traderegister Tilburg: 18070844 \ IBAN: NL13 RABO 0143 0035 26 \ BIC: RABONL2U \ VAT: NL 8123.91.755.B01

www.vandelande.com

All our transactions are subject to the Van de Lande General Terms of Sale. A copy of these can be provided immediately upon your request.