





按图定制

①代号	边长	④材质	⑤表面处理	最高使用压力
MAHBEJT	25×25	铝合金	本色阳极氧化	1MPa(≈10.2Kgf/cm²)以下
MAHBEJP	30×40			
MAHBEJR	50×50			

⚠ 由于批次不同, 发货带表面处理产品可能存在色差, 不影响尺寸及功能。



①代号 - ②侧面孔数K - ③S - ④T - ⑤Z - ⑥Y  
 MAHBEJP - K3 - S1 - T1 - Z1N - Y5

①代号	②侧面孔数K	RC(PT)/M选择				间距 P	N	螺孔数
		③S	④T	⑤Z	⑥Y			
MAHBEJT (25×25)	1					15	0	4
	2						1	6
	3			1 (1/8)			2	8
	4			3M (M3)			3	10
	5			4M (M4)			4	12
	6			5 (M5)			5	14

⚠ 侧面孔数为“6”时,L/2位置增加一个适用M5螺钉的安装孔。

①代号	②侧面孔数K	RC(PT)/M/NPT选择				间距 P	N	螺孔数
		③S	④T	⑤Z	⑥Y			
MAHBEJP (30×40)	1					30	0	4
	2						1	6
	3			1 (1/8)			2	8
	4			2 (1/4)			3	10
	5			5 (M5)			4	12
	6			1N (NPT1/8)			5	14

⚠ 侧面孔数为“6”时,L/2位置增加一个适用M5螺钉的安装孔。

①代号	②侧面孔数K	RC(PT)选择				间距 P	N	螺孔数
		③S	④T	⑤Z	⑥Y			
MAHBEJR (50×50)	1					40	0	4
	2						1	6
	3			2 (1/4)			2	8
	4			3 (3/8)			3	10
	5			4 (1/2)			4	12
	6						5	14

⚠ 侧面孔数为“6”时,L/2位置增加一个适用M8螺钉的安装孔。



爱安特自制模组, 火爆开售! 全零件备库, 最快 5 个工作日出货!



400-6699-428



www.ant-fa.com

L5  
歧管块