


SCREW FOR T-SLOT, DIN 787

2140.30.



Material:

heat-treated,
M 8 – M12 to strength class 10.9
M14 – M30 to strength class 8.8

Execution:

forged, thread rolled, T-slot milled

2140.30. Screw for T-slot, DIN 787

Order No	a ₁	a	b	d ₁	e	k	l	Order No	a ₁	a	b	d ₁	e	k	l
2140.30.08.08.032	8	7.7	22	8	13	6	32	2140.30.20.20.125	20	19.7	85	20	32	12	125
2140.30.08.08.050	8	7.7	35	8	13	6	50	2140.30.20.20.160	20	19.7	110	20	32	12	160
2140.30.08.08.080	8	7.7	50	8	13	6	80	2140.30.20.20.200	20	19.7	125	20	32	12	200
2140.30.10.10.040	10	9.7	30	10	15	6	40	2140.30.20.20.250	20	19.7	150	20	32	12	250
2140.30.10.10.063	10	9.7	45	10	15	6	63	2140.30.20.20.315	20	19.7	190	20	32	12	315
2140.30.10.10.100	10	9.7	60	10	15	6	100	2140.30.20.22.080	22	21.7	55	20	35	14	80
2140.30.12.12.050	12	11.7	35	12	18	7	50	2140.30.20.22.100	22	21.7	65	20	35	14	100
2140.30.12.12.063	12	11.7	40	12	18	7	63	2140.30.20.22.125	22	21.7	85	20	35	14	125
2140.30.12.12.080	12	11.7	55	12	18	7	80	2140.30.20.22.160	22	21.7	110	20	35	14	160
2140.30.12.12.125	12	11.7	75	12	18	7	125	2140.30.20.22.200	22	21.7	125	20	35	14	200
2140.30.12.12.200	12	11.7	120	12	18	7	200	2140.30.20.22.250	22	21.7	150	20	35	14	250
2140.30.12.14.050	14	13.7	35	12	22	8	50	2140.30.20.22.315	22	21.7	190	20	35	14	315
2140.30.12.14.063	14	13.7	45	12	22	8	63	2140.30.24.24.100	24	23.7	70	24	40	16	100
2140.30.12.14.080	14	13.7	55	12	22	8	80	2140.30.24.24.125	24	23.7	85	24	40	16	125
2140.30.12.14.125	14	13.7	75	12	22	8	125	2140.30.24.24.160	24	23.7	110	24	40	16	160
2140.30.12.14.200	14	13.7	120	12	22	8	200	2140.30.24.24.200	24	23.7	125	24	40	16	200
2140.30.14.16.063	16	15.7	45	14	25	9	63	2140.30.24.24.250	24	23.7	150	24	40	16	250
2140.30.14.16.100	16	15.7	65	14	25	9	100	2140.30.24.24.315	24	23.7	190	24	40	16	315
2140.30.14.16.160	16	15.7	125	14	25	9	160	2140.30.24.24.400	24	23.7	240	24	40	16	400
2140.30.14.16.250	16	15.7	150	14	25	9	250	2140.30.24.28.100	28	27.7	70	24	44	18	100
2140.30.16.16.063	16	15.7	45	16	25	9	63	2140.30.24.28.125	28	27.7	85	24	44	18	125
2140.30.16.16.080	16	15.7	55	16	25	9	80	2140.30.24.28.160	28	27.7	110	24	44	18	160
2140.30.16.16.100	16	15.7	65	16	25	9	100	2140.30.24.28.200	28	27.7	125	24	44	18	200
2140.30.16.16.160	16	15.7	100	16	25	9	160	2140.30.24.28.250	28	27.7	150	24	44	18	250
2140.30.16.16.200	16	15.7	125	16	25	9	200	2140.30.24.28.315	28	27.7	190	24	44	18	315
2140.30.16.16.250	16	15.7	150	16	25	9	250	2140.30.24.28.400	28	27.7	240	24	44	18	400
2140.30.16.18.063	18	17.7	45	16	28	10	63	2140.30.30.36.125	36	35.6	80	30	54	22	125
2140.30.16.18.080	18	17.7	55	16	28	10	80	2140.30.30.36.160	36	35.6	110	30	54	22	160
2140.30.16.18.100	18	17.7	65	16	28	10	100	2140.30.30.36.200	36	35.6	135	30	54	22	200
2140.30.16.18.160	18	17.7	100	16	28	10	160	2140.30.30.36.250	36	35.6	150	30	54	22	250
2140.30.16.18.200	18	17.7	125	16	28	10	200	2140.30.30.36.315	36	35.6	200	30	54	22	315
2140.30.16.18.250	18	17.7	150	16	28	10	250	2140.30.30.36.500	36	35.6	300	30	54	22	500
2140.30.20.20.080	20	19.7	55	20	32	12	80								
2140.30.20.20.100	20	19.7	65	20	32	12	100								