


带喇叭颈的冲头，毛坯，DIN 5118 A 型

2206.




2206. 带喇叭颈的冲头，毛坯，DIN 5118 A 型

d ₁ / 订购数字	d ₂	a	k	r	l (订货字母)	71 (D)	80 (E)	90 (F)	100 (G)	120 (J)	150 (M)	200 (N)
3/(1)	4.5	1	3	6.5		●	●	●	●	●		
4/(2)	5.5	1.5	4	8		●	●	●	●	●		
5/(3)	7	1.5	4	10		●	●	●	●	●		
6/(4)	9	1.5	4	10		●	●	●	●	●		
8/(5)	11	1.5	4	12		●	●	●	●	●		
10/(6)	14	1.5	4	15		●	●	●	●	●	●	
13/(7)	17	1.5	4	15		●	●	●	●	●	●	●
16/(8)	20	1.5	4	15		●	●	●	●	●	●	●
20/(9)	25	1.5	4	15		●	●	●	●	●	●	●

订购示例:

2 2 0 6 . 7 G



长度: l
100 mm
直径: d₁
13 mm
型号:
带锥形头
规格:
毛坯
冲头:

订货字母
= (G)
订购数字
= (7)
订购数字
= (6)
订购数字
= (0)
无弹顶销
= 22

材料:

HSS

硬度:

杆部 62-66 HRC

头部 45-55 HRC

材料说明和其他材料见E章开头。

结构:

凸模杆部已精磨。凸模头部已热锻并退火。

说明:

匹配的先导式总钻 2284.00.