


# 带有抛物线形头部的导正销, ISO 8020



2271.



2271. 带有抛物线形头部的导正销, ISO 8020

d <sub>1</sub> / 订购数字	d <sub>2</sub>	T	P	l <sub>1</sub> / 订购数字	l / (订货字母)	50 (A)	56 (B)	63 (C)	71 (D)	80 (E)	90 (F)	100 (G)
5 / (3)	8	5	1 - 4,9	10 (2) 13 (3)		●	●	●	●			
6 / (4)	9	5	1,6 - 5,9	10 (2) 13 (3)		●	●	●	●	●		
8 / (5)	11	5	2,5 - 7,9	10 (2) 13 (3)		●	●	●	●	●		
10 / (6)	13	5	4 - 9,9	10 (2) 13 (3) 19 (4)		●	●	●	●	●	●	●
13 / (7)	16	5	5 - 12,9	10 (2) 13 (3) 19 (4)		●	●	●	●	●	●	●
16 / (8)	19	5	8 - 15,9	13 (3) 19 (4)		●	●	●	●	●	●	●
20 / (9)	23	5	12 - 19,9	13 (3) 19 (4)			●	●	●	●	●	●
25 / (10)	28	5	16,5 - 24,9	13 (3) 19 (4)			●	●	●	●	●	●
32 / (11)	35	5	20 - 31,9	19 (4)					●	●	●	●

**材料:**

HSS

**硬度:**

杆部 64 ± 2 HRC

头部 52 ± 5 HRC

**结构:**

头部热墩。肩部、轴部及前端精磨加工。

特别生产请咨询。

**说明:**

2 mm 长度作用纯粹为导向 它先于冲压凸模和板材接触。

**抛物线长度可选范围:**


= 8 mm 当 P ≤ 10 mm

= 12 mm 当 P 10,1 mm - 15 mm

= 15 mm 当 P > 15 mm

**订购示例:**

2 2 7 1 . 9 F 4 . 1 8 7 0



形状: 圆形

P = ∅ 18,7 mm

冲裁凸模长度: l<sub>1</sub>

19 mm

长度: l

90 mm

直径: d<sub>1</sub>

20 mm

型号:

ISO

规格:

抛物面尖部导正销

冲头:

无弹顶销

= 1870

订购数字

= (4)

订货字母

= (F)

订购数字

= (9)

订购数字

= (1)

订购数字

= (7)

= 22