


## 快速更换型冲头，阶梯式，圆形，重载荷用



2213.



2213. 快速更换型冲头，阶梯式，圆形，重载荷用

d <sub>2</sub> / 订购数字	d <sub>5</sub>	P	l <sub>1</sub> / 订购数字	l (订货字母)	63 (C)	71 (D)	80 (E)	90 (F)	100 (G)	110 (H)	125 (J)
10 / (2)	10	1,6 - 9,9	13(1) 19(2)		●	●	●	●	●	●	●
13 / (3)	12	5 - 12,9	13(1) 19(2)		●	●	●	●	●	●	●
16 / (4)	12	8 - 15,9	13(1) 19(2) 25(3)		●	●	●	●	●	●	●
20 / (5)	12	12 - 19,9	13(1) 19(2) 25(3)		●	●	●	●	●	●	●
25 / (6)	12	16 - 24,9	13(1) 19(2) 25(3)			●	●	●	●	●	●
32 / (7)	12	24 - 31,9	13(1) 19(2) 25(3)			●	●	●	●	●	●
40 / (9)	12	30 - 39,9	19(2) 25(3) 30(4)				●	●	●	●	●

l<sub>1</sub>=10 当 P < 2.20

### 材料:


HSS  
硬度 62 ± 2 HRC

### 结构:

精磨凸模柄部和凸模切削刃直径。  
特别尺寸请洽询

### 订购示例:

2 2 1 3 . 7 G 2 . 2 4 5 0



形状: 圆形  
P = ∅ 24,5 mm  
冲裁凸模长度: l<sub>1</sub>  
19 mm  
长度: l  
100 mm  
直径: d<sub>2</sub>  
32 mm  
型号:  
重型  
规格:  
圆形  
冲头:  
无弹顶销

= 2450  
订购数字  
= (2)  
订货字母  
= (G)  
订购数字  
= (7)  
订购数字  
= (3)  
订购数字  
= (1)  
= 22