

GAS SPRING, STANDARD

Note:

Initial spring force at 150 bar = 10000 daN

Order No for spare parts kit: 2480.12.10000

Gas spring without valve

Order No (example): 2480.12.10000. .P

Gas spring to Renault standard EM24.54.700

Order No (example): 2480.12.10000. .R

Gas spring to Renault standard EM24.54.700 without valve

Order No (example): 2480.12.10000. .R.P

Pressure medium: Nitrogen N₂

Max. filling pressure: 150 bar

Min. filling pressure: 25 bar

Working temperature: 0°C to +80°C


Temperature related force increase: ± 0.3%/°C

Max. recommended extensions per minute:


approx. 15 to 40 (at 20°C)

Max. piston speed: 1.6 m/s

2480.12.10000.



View X - Gas spring




2480.12.10000.


Gas spring, Standard

Order No	Stroke _{max.} (s)	l _{min.}	l
2480.12.10000.025	25	185	210
2480.12.10000.038	38.1	198.1	236.2
2480.12.10000.050	50	210	260
2480.12.10000.063	63.5	223.5	287
2480.12.10000.080	80	240	320
2480.12.10000.100	100	260	360
2480.12.10000.125	125	285	410
2480.12.10000.160	160	320	480
2480.12.10000.200	200	360	560
2480.12.10000.250	250	410	660
2480.12.10000.300	300	460	760

Initial spring force versus charge pressure



Spring force Diagram displacement versus stroke rise



Pressure rise factor accounts for displacement but not external influences!