



带氮气弹簧的弹簧冲压件



安装示例



2478.



材料:

C45
 感应加热淬火 58+4 HRC
 淬火深度 0,8+0,4

用固体润滑剂的滑动表面

2478. 带氮气弹簧的弹簧冲压件

订购编号	冲程 _{max.}	$l_{min.}$	l_1	l_2	负载/力 [daN]		氮气弹簧
					开始	结束	
2478.050.00030.1	50	92	257	150	30	40	2482.74.00030.050.2
2478.050.00050.1	50	92	257	150	50	67	2482.74.00050.050.2
2478.050.00070.1	50	92	257	150	70	94	2482.74.00070.050.2
2478.050.00090.1	50	92	257	150	90	120	2482.74.00090.050.2
2478.063.00030.1	63	109	310	190	30	40	2482.74.00030.063.2
2478.063.00050.1	63	109	310	190	50	67	2482.74.00050.063.2
2478.063.00070.1	63	109	310	190	70	94	2482.74.00070.063.2
2478.063.00090.1	63	109	310	190	90	120	2482.74.00090.063.2
2478.080.00030.1	80	125	360	223	30	40	2482.74.00030.080.2
2478.080.00050.1	80	125	360	223	50	67	2482.74.00050.080.2
2478.080.00070.1	80	125	360	223	70	94	2482.74.00070.080.2
2478.080.00090.1	80	125	360	223	90	120	2482.74.00090.080.2