




Blindnietmutter AFM

Serie 10.850



Aluminium

- > Flachkopf
- > Rundschaft
- > offen



EN AW - 5754 [AlMg3]

M	\pm	I	Nr.		
M3	0,3 - 1,0	7,5	10.850.030.100	500	
	0,3 - 2,0	8,5	10.850.030.200	500	
	2,0 - 3,5	12,0	10.850.030.350	500	
D 5,0	k 0,8	dk 7,0	l₁ max. 6,0	\curvearrowright 1 Nm	\updownarrow 1500 N
M4	0,5 - 3,0	11,0	10.850.040.300	500	
	2,5 - 4,0	12,0	10.850.040.400	500	
	3,0 - 5,0	14,0	10.850.040.500	500	
D 6,0	k 0,8	dk 10,0	l₁ max. 8,0	\curvearrowright 3 Nm	\updownarrow 2600 N
M5	0,5 - 3,0	12,0	10.850.050.300	500	
	3,0 - 4,0	13,0	10.850.050.400	500	
	2,5 - 4,5	14,5	10.850.050.450	500	
	4,0 - 6,0	16,0	10.850.050.600	500	
D 7,0	k 1,0	dk 11,0	l₁ max. 9,0	\curvearrowright 4 Nm	\updownarrow 4300 N

NEU

NEU

NEU

NEU

NEU

M	\pm	I	Nr.		
M6	0,5 - 3,0	14,5	10.850.060.300	500	
	3,0 - 4,5	16,0	10.850.060.450	500	
D 9,0	k 1,5	dk 13,0	l₁ max. 11,0	\curvearrowright 6 Nm	\updownarrow 6700 N
M8	0,5 - 3,0	17,0	10.850.080.300	500	
	3,0 - 5,5	19,5	10.850.080.550	500	
	5,5 - 7,5	21,5	10.850.080.750	500	
D 11,0	k 1,5	dk 16,0	l₁ max. 13,5	\curvearrowright 18 Nm	\updownarrow 11000 N
M10	0,5 - 3,0	17,0	10.850.100.300	250	
	2,0 - 4,5	22,0	10.850.100.450	250	
	3,0 - 6,0	26,0	10.850.100.600	250	
D 13,0	k 2,0	dk 19,0	l₁ max. 16,5	\curvearrowright 28 Nm	\updownarrow 17500 N
M12	1,0 - 4,0	26,0	10.850.120.400	250	
	3,5 - 7,0	29,0	10.850.120.700	100	
D 16,0	k 2,0	dk 23,0	l₁ max. 18,5	\curvearrowright 45 Nm	\updownarrow 28000 N

NEU