




Blind Rivet Nut EFM A4

Series 10.858/79 **NEW**

Stainless Steel A4

- > Flat Head
- > Round Shank
- > Open



| M | | l | No. | |
|--------------|--------------|----------------|--------------------|---------------|
| M4 | 0,5 - 2,0 | 11,0 | 10.858.040.200/79 | 500 |
| D 6,0 | k 0,8 | dk 9,0 | l1 max. 8,0 | 5 Nm 7000 N |
| M5 | 0,5 - 2,0 | 13,0 | 10.858.050.200/79 | 500 |
| D 7,0 | k 1,0 | dk 10,0 | l1 max. 8,0 | 8 Nm 11000 N |

NEW

| M | | l | No. | |
|---------------|--------------|----------------|---------------------|----------------|
| M6 | 0,5 - 2,5 | 15,0 | 10.858.060.250/79 | 500 |
| D 9,0 | k 1,3 | dk 12,0 | l1 max. 10,0 | 15 Nm 18000 N |
| M8 | 0,5 - 3,5 | 20,0 | 10.858.080.350/79 | 500 |
| D 11,0 | k 1,5 | dk 15,0 | l1 max. 11,5 | 26 Nm 27000 N |

NEW

NEW