




Blind Rivet Nut HEXAFORM® KLSK

Series 10.892



Steel

- > Small Countersunk Head
- > Hexagonal Shank
- > Open



C4C [1.0303]

M		l	No.	
M3	2,0 - 3,0	9,7	10.892.030.250	500
SW 5,0	SW ² 6,0	k 0,5	l ₁ max. 4,5	1,2 Nm 3500 N
M4	0,6 - 2,0	11,0	10.892.040.200	500
SW 6,0	SW ² 6,6	k 0,6	l ₁ max. 7,5	5 Nm 5000 N
M5	0,5 - 3,0	13,5	10.892.050.300	500
SW 7,0	SW ² 7,7	k 0,7	l ₁ max. 8,5	7 Nm 9000 N
M6	0,8 - 3,0	15,5	10.892.060.300	500
	3,0 - 5,5	18,0	10.892.060.550	500
SW 9,0	SW ² 9,8	k 0,8	l ₁ max. 10,5	13 Nm 16000 N

NEW

M		l	No.	
M8	0,8 - 3,0	18,5	10.892.080.300	250
	3,0 - 6,0	21,5	10.892.080.600	250
SW 11,0	SW ² 11,8	k 0,8	l ₁ max. 13,0	25 Nm 23000 N
M10	1,0 - 3,5	22,5	10.892.100.350	250
	3,0 - 6,0	23,5	10.892.100.600	250
SW 13,0	SW ² 14,3	k 0,9	l ₁ max. 16,5	55 Nm 36500 N
M12	1,0 - 4,0	24,5	10.892.120.400	100
SW 16,0	SW ² 17,3	k 0,9	l ₁ max. 17,5	85 Nm 55000 N

NEW