




Blind Rivet Nut EFM

Series 10.858

Stainless Steel A2

- > Flat Head
- > Round Shank
- > Open



[1.4567]

M		l	No.			
M3	0,5 - 2,0	9,0	10.858.030.200	500		
D	5,0	k 0,8	d _k 8,0	l ₁ max. 7,0	⌀ 2 Nm	↑ 4500 N
M4	0,5 - 2,5	11,0	10.858.040.250	500		
	2,5 - 4,0	12,5	10.858.040.400	500		
D	6,0	k 1,0	d _k 9,0	l ₁ max. 8,0	⌀ 4 Nm	↑ 7000 N
M5	0,5 - 3,0	12,0	10.858.050.300	500		
	3,0 - 4,5	13,5	10.858.050.450	500		
D	7,0	k 1,5	d _k 10,0	l ₁ max. 8,5	⌀ 6 Nm	↑ 11000 N
M6	0,5 - 3,0	14,0	10.858.060.300	500		
	3,0 - 5,0	16,0	10.858.060.500	500		
D	9,0	k 1,5	d _k 12,0	l ₁ max. 10,0	⌀ 11 Nm	↑ 18000 N

NEW

NEW

NEW

M		l	No.			
M8	0,5 - 3,0	16,0	10.858.080.300	500		
	3,0 - 5,5	18,5	10.858.080.550	250		
D	11,0	k 1,5	d _k 15,0	l ₁ max. 11,5	⌀ 24 Nm	↑ 27000 N
M10	1,0 - 3,5	19,0	10.858.100.350	250		
	D	13,0	k 2,0	d _k 17,0	l ₁ max. 14,0	⌀ 50 Nm
M12	1,0 - 4,0	26,0	10.858.120.400	100		
	D	16,0	k 2,0	d _k 23,0	l ₁ max. 16,5	⌀ 85 Nm