


Elastomerkupplung kompakt

Halbschalenausführung

optional komplett in Edelstahl



Bestellbeispiel

KBE2HC - 19 - 10 - 12 - 98Sh

Typ Größe ØD1 (H7) ØD2 (H7) Shorehärte

Größe	Abmessungen (mm)											Maximaldrehzahl rpm. (1/min)	Masse (pro Kupplung) (g)	Massenträgheitsmoment (pro Kupplung) J (g m²)	Drehmoment (Nm)	
	Ø A	L	Ø D1/D2		E	W	F	K	C	B	H					G
			Bohrungen	min												
14	30	32	4	16	9.5	16.4	13	7.8	4.5	35	10.5	M4 4.5	13000	47	0.006	12.5
19	40	50	8	21	17	21	16	14.5	8.0	46	14.5	M6 15	10000	79	0.019	17
24	55	58	10	32	20	26	18	16	8	57.5	20	M6 15	7000	280	0.121	60
28	65	62	14	37	21	28	20	17	9	73	25	M8 40	6000	421	0.266	160
38	80	86	18	48	31	38	24	24	12	83.5	30	M8 40	5000	840	0.790	325
42	95	94	22	50	34.5	44	25	25	12.5	93.5	32	M10 84	4000	1416	1.832	450
48	105	110	22	57	41	50	28	30	14	105	36	M12 145	3750	1956	3.101	525

Größe	Ø Bohrung (mm)																									
	4	6	8	10	11	14	15	16	18	19	20	22	24	25	28	30	32	35	38	40	42	45	46	48	50	55
14	10.3	15.5	20.7	25.8	28.4	36.1	38.7	41.3																		
19			47	59	65	83	89	95	107	113	119															
24				59	65	83	89	95	107	113	119	130	142	148	166	178	190									
28						123	132	141	159	167	176	194	211	220	247	264	282	308	335							
38									159	167	176	194	211	220	247	264	282	308	335	352	370	396	405	423		
42												370	404	420	471	505	538	589	639	673	706	757	774	807	841	
48												539	588	612	686	735	784	857	931	980	1029	1102	1127	1176	1225	1347

+ **Material** Nabe - Aluminium
 Zahnkranz - Polyurethan
Nabe Bohrungstoleranz: H7
Passfedernut wahlweise nach DIN 6885
Shorehärte 98 Sh A (rot)
Weitere Shorehärten und technische Daten
finden Sie auf Seite 42.