


Part No. structure



Series 255 - snap-open along outer radius

Part No.	B_i [mm]	B_a [mm]	R [mm]	Bending radii									Weight [kg/m]
255.03.□.0	38	54	055	075	100	125	150	175	200	225	250	≈ 0,81	
255.05.□.0	57	73	055	075	100	125	150	175	200	225	250	≈ 0,90	
255.07.□.0	77	93	055	075	100	125	150	175	200	225	250	≈ 1,01	
255.10.□.0	103	119	055	075	100	125	150	175	200	225	250	≈ 1,15	

Supplement Part No. with required radius. Example: 255.03.055.0

0 = standard color, other colors ► page 1.39 · Pitch = 27,8 mm/link - Links/m = 36

