


E4.1 | e-chains® E4.32·H4.32 | Accessories

KMA mounting brackets | Attachment from any side | Pivoting | Locking



Standard

KMA pivoting | Recommended for unsupported and gliding applications

KMA locking | Recommended for vertical hanging and standing applications

Width index	Part No. full set KMA pivoting	Part No. full set KMA locking	Bi [mm]	Width index	Part No. full set KMA pivoting	Part No. full set KMA locking	Bi [mm]
05.	E4.320.05 .12.C	E4.321.05 .12.C	50	212.	E4.320.212 .12.C	E4.321.212 .12.C	212
06.	E4.320.06 .12.C	E4.321.06 .12.C	68	23.	E4.320.23 .12.C	E4.321.23 .12.C	225
07.	E4.320.07 .12.C	E4.321.07 .12.C	75	237.	E4.320.237 .12.C	E4.321.237 .12.C	237
087.	E4.320.087 .12.C	E4.321.087 .12.C	87	25.	E4.320.25 .12.C	E4.321.25 .12.C	250
09.	E4.320.097 .12.C	E4.321.097 .12.C	97	262.	E4.320.262 .12.C	E4.321.262 .12.C	262
10.	E4.320.10 .12.C	E4.321.10 .12.C	100	28.	E4.320.28 .12.C	E4.321.28 .12.C	275
11.	E4.320.11 .12.C	E4.321.11 .12.C	108	29.	E4.320.29 .12.C	E4.321.29 .12.C	287
112.	E4.320.112 .12.C	E4.321.112 .12.C	112	30.	E4.320.30 .12.C	E4.321.30 .12.C	300
12.	E4.320.12 .12.C	E4.321.12 .12.C	125	312.	E4.320.312 .12.C	E4.321.312 .12.C	312
137.	E4.320.137 .12.C	E4.321.137 .12.C	137	325.	E4.320.325 .12.C	E4.321.325 .12.C	325
15.	E4.320.15 .12.C	E4.321.15 .12.C	150	337.	E4.320.337 .12.C	E4.321.337 .12.C	337
162.	E4.320.162 .12.C	E4.321.162 .12.C	162	350.	E4.320.350 .12.C	E4.321.350 .12.C	350
17.	E4.320.17 .12.C	E4.321.17 .12.C	168	362.	E4.320.362 .12.C	E4.321.362 .12.C	362
18.	E4.320.18 .12.C	E4.321.18 .12.C	175	375.	E4.320.375 .12.C	E4.321.375 .12.C	375
187.	E4.320.187 .12.C	E4.321.187 .12.C	187	387.	E4.320.387 .12.C	E4.321.387 .12.C	387
20.	E4.320.20 .12.C	E4.321.20 .12.C	200	400.	E4.320.400 .12.C	E4.321.400 .12.C	400

(KMA = polymer metal mounting bracket) For the C-profile option please add index **C**