

# Interior installation

## Assembly components



### Mounting bracket TS

Offers variable mounting opportunities for the mounting angle 23 x 23 mm.  
E.g. for supporting external surfaces or creating an additional internal level.




**Material:**  
Die-cast zinc

**Supply includes:**  
24 screws 5.5 x 13 mm.

Packs of	Model No. TS
24	8800.370

#### + Accessories:

U nuts (recommendation: M6),  
see page 1010.



#### Installation options:

- On the vertical TS enclosure section
  - flush with the outer edge of the enclosure or
  - flush with the enclosure clearance width.

#### 1 Support of the external surfaces with two mounting options:

- Without mounting plate (photo)
- With mounting plate (drawing)

Two installation options for the inner mounting level:

#### 2 If there is no divider panel fitted.

#### 3 With a divider panel fitted, and without or with a mounting plate in a set forward position.



### Mounting bracket PS

For variable attachment of punched rails 23 x 23 mm.

#### Installation options:

- Optionally flush with:
  - Outer enclosure edge or
  - Enclosure clearance width
- On the vertical TS enclosure section via
  - Adaptor rail for PS compatibility, see page 997
- On the horizontal TS enclosure section
- On enclosures and rails with rectangular system punching 12.5 x 10.5 mm.

**Material:**  
Die-cast zinc

**Supply includes:**  
1 set =  
1 mounting bracket,  
1 screw M6 x 12 mm,  
1 cage nut M6.

Packs of	Model No. PS
24 sets	4182.000

#### ! Also required:

U nuts for punched rails (recommended: M6),  
see page 1010.  
Multi-tooth screws M6 x 12 mm,  
see page 1011.