

SERIES 66

“TR” POLYURETHANE WHEELS WITH POLYAMIDE 6 CENTRE



Wheel description

“TR” polyurethane tread, hardness 95+/-3 Shore A; excellent rolling resistance and elasticity, highly resistant to wear and to tearing.

Hub

The hub is available with plain bearing, with roller bearing, with stainless steel roller bearing, with ball bearing and with ball bearing facilities.

Diameters: 80-250 mm

Carrying capacity: 150-1000 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm
Models available: with top plate fastening, with bolt hole
Suitable brakes: front-locking and central (hexagonal) brake systems



Medium duty brackets type M

Max. carrying capacity 500 daN – available diameters 150-200 mm
Models available: with top plate fastening
Suitable brakes: adjustable front-locking brake



Medium-heavy duty brackets type P - PX

Max. carrying capacity 750 daN – available diameters 80-200 mm
Models available: with top plate fastening
Suitable brakes: front-locking and adjustable rear-locking brake systems

Uses

Environments

Suitable for environment with atmospheric agents, alcohol and glycol; not suitable for applications where mineral and organic acids, base solutions and saturated vapour are present.

Usage temperatures: from -20 °C to +80 °C

Floors



Handling

